



SPECIFICATION SHEET

64-V2000

AMBI-DEX® INDUSTRIAL GRADE DISPOSABLE VINYL GLOVES, POWDERED – 4 MIL

- Made from a soft-virgin vinyl formulation specially compounded to deliver an optimal combination of comfort, fit, flexibility, tactile sensitivity and performance
- Rolled beaded cuff adds additional strength to cuff edge for longer glove life and prevents liquid run-off
- Translucent white color
- Contains no natural rubber latex proteins
- Ambidextrous and synthetic polymer coating for ease of donning and doffing
- DEHP & DOP Free
- Made from component materials that comply with Federal Regulations for food contact 21 CFR, 170-199

APPLICATIONS

- Light hand protection
- Liquids
- Debris

CARE INSTRUCTIONS

Hand wash only, do not bleach, hang dry.

TECHNICAL DATA

MATERIAL	Vinyl				
COLOR	☐ Clear				
CUFF STYLE	Rolled beaded				
SIZES	S - XXL				
PACKAGING	100 gloves per box, 10 boxes per case				
CASE DIMENSIONS	10.4" x 10.0" x 14.5" / 26.5cm x 25.5cm x 36.8cm				
CASE WEIGHT	S	M	L	XL	XXL
	13 lbs 5.89 kg	14 lbs 6.35 kg	15 lbs 6.8 kg	16 lbs 7.25 kg	17 lbs 7.71 kg
COO	China				

BARCODES

ITEM	BAG	DISPENSER	CASE
☐ 64-V2000/S	---	01616314014444	02616314014444
☐ 64-V2000/M	---	01616314014451	02616314014451
☐ 64-V2000/L	---	01616314014468	02616314014468
☐ 64-V2000/XL	---	01616314014475	02616314014475
☐ 64-V2000/XXL	---	01616314014482	02616314014482



DIMENSIONS (in/cm)

	S	M	L	XL	XXL
A	9.4 / 24	9.4 / 24	9.4 / 24	9.4 / 24	9.4 / 24
B	3.3 / 8.5	3.7 / 9.5	4.1 / 10.5	4.5 / 11.5	4.92 / 12.5

