



# SPECIFICATION SHEET

## 68-163SB

### REGULAR GRADE TOP GRAIN / SHOULDER SPLIT COWHIDE LEATHER DRIVER'S GLOVE WITH KEVLAR® STITCHING - KEYSTONE THUMB

- Top grain/shoulder split cowhide leather construction provides comfort, durability, excellent abrasion resistance, and breathability
- Top grain leather palm is smooth, provides durability and dexterity
- Shoulder split leather back makes this glove more economical than full top grain construction
- Stitched with Kevlar® adding strength and burn resistance
- Drivers gloves feature slip-on styling to provide good fit and comfort
- Keystone thumb is ergonomic, reduces hand fatigue, offers superior dexterity and durability
- Leather wrapped index finger for extra protection
- Elastic closure sewn inside glove for safety and comfort
- Rolled leather cuff for longer wear

### APPLICATIONS

- Construction
- Machine operation
- Light duty welding
- Utility work
- Farming
- Roping

### TECHNICAL DATA

|                 |                                      |                                            |                   |                   |
|-----------------|--------------------------------------|--------------------------------------------|-------------------|-------------------|
| MATERIAL        | Cowhide leather                      |                                            |                   |                   |
| CONSTRUCTION    | 100% leather, Kevlar® stitching      |                                            |                   |                   |
| COLOR           | Natural with Gray                    |                                            |                   |                   |
| CUFF STYLE      | Slip On                              |                                            |                   |                   |
| SIZES           | S - XL                               |                                            |                   |                   |
| PACKAGING       | 12 pair per dozen, 10 dozen per case |                                            |                   |                   |
| CASE DIMENSIONS | S                                    | 24.8" x 9.8" x 10.2" / 63cm x 25cm x 26cm  |                   |                   |
|                 | M                                    | 25.2" x 10.2" x 10.2" / 64cm x 26cm x 26cm |                   |                   |
|                 | L                                    | 25.6" x 10.6" x 10.2" / 65cm x 27cm x 26cm |                   |                   |
|                 | XL                                   | 25.6" x 11" x 10.2" / 65cm x 28cm x 26cm   |                   |                   |
| CASE WEIGHT     | S                                    | M                                          | L                 | XL                |
|                 | 31 lbs<br>14 kg                      | 34.7 lbs<br>15.7 kg                        | 39 lbs<br>17.7 kg | 43 lbs<br>19.5 kg |
| COO             | India                                |                                            |                   |                   |

### BARCODES

| ITEM        | BAG  | DOZEN          | CASE           |
|-------------|------|----------------|----------------|
| 68-163SB/S  | ---- | 01616314008680 | 02616314008680 |
| 68-163SB/M  | ---- | 01616314008597 | 02616314008597 |
| 68-163SB/L  | ---- | 01616314008603 | 02616314008603 |
| 68-163SB/XL | ---- | 01616314008610 | 02616314008610 |



### DIMENSIONS (in/cm)

|          | S          | M          | L          | XL         |
|----------|------------|------------|------------|------------|
| <b>A</b> | 8.8 / 22.3 | 9.3 / 23.5 | 9.8 / 24.8 | 10.2 / 26  |
| <b>B</b> | 4.5 / 11.5 | 4.8 / 12.3 | 5 / 12.8   | 5.2 / 13.3 |

