



SPECIFICATION SHEET

73-2000



FR Treated Hi-Performance Goatskin Leather Palm Glove with Aramid Back and TPR Protection

- FR treated synthetic goatskin leather palm for heat protection
- Aramid fabric back for added heat resistance and strength
- Digitized goatskin leather grip for on palm and fingers for enhanced handling power
- Internal foam padded palm absorbs and dampens shock
- Thermo Plastic Rubber (TPR) protection on fingers, knuckles and back of hand for pinch point and dorsal protection
- Reinforced thumb crotch for extended glove life, enhanced comfort, increased abrasion resistance and added durability in a high-wear area
- Stitched with Kevlar® adding strength and burn resistance
- Slip-On cuff allows for easy on and off

APPLICATIONS

- Material handling
- Stamping
- Grinding
- Cut resistance
- Multi-tasking where welding could be part of the task

CARE INSTRUCTIONS

Hand wash in cold water. Do not bleach. Hang dry; tumble dry is not recommended. Do not iron.

TECHNICAL DATA

MATERIAL	Goatskin leather / Aramid fabric back		
COLOR	■ Black		
CUFF STYLE	Slip-on		
SIZES	M - XL		
PACKAGING	12 pairs per dozen, 4 dozen per case		
CASE	19.7" x 11.8" x 18.9" / 50cm x 30cm x 48cm		
CASE WEIGHT	M	L	XL
	29.5 lbs	30.6 lbs	32.0 lbs
	13.4 kg	13.9 kg	14.5 kg
COO	China		

PERFORMANCE PROPERTIES

EN388: 3122						
ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-



BARCODES

ITEM	PAIR	DOZEN	CASE
■ 73-2000/M	616314190841	01616314190840	02616314190849
■ 73-2000/L	616314190834	01616314190833	02616314190832
■ 73-2000/XL	616314190858	01616314190857	02616314190856

DIMENSIONS (in/cm)

	M	L	XL	---	---	---
A	11.0 / 28	11.4 / 29	11.8 / 30	---	---	---
B	4.7 / 12	4.9 / 12.5	5.1 / 13	---	---	---

