



SPECIFICATION SHEET

77-238

REGULAR GRADE SPLIT COWHIDE LEATHER GLOVE WITH WHITE THERMAL LINING - STRAIGHT THUMB

- Split Cowhide leather construction provides comfort, durability, excellent abrasion resistance, and breathability
- Split leather is economical and has a visible texture
- White thermal lining provides insulation
- Drivers gloves feature slip-on styling to provide good fit and comfort
- Straight thumb increases comfort in closed-fisted work
- Elastic closure sewn inside glove for safety and comfort
- Cotton color binding denotes sizing

APPLICATIONS

- Farming
- Construction
- Machine operation
- Refrigeration
- Other cold weather applications

TECHNICAL DATA

MATERIAL	Cowhide leather			
CONSTRUCTION	100% leather with thermal lining			
COLOR	■ Tan			
CUFF STYLE	Slip on			
SIZES	S - XL			
PACKAGING	12 pairs per dozen, 6 dozen per case			
CASE (in/cm)	(S) 10.2 x 16.1 x 16.5 / 26 x 41 x 42			
	(M) 10.6 x 16.5 x 16.5 / 27 x 42 x 42			
	(L) 11 x 16.9 x 16.5 / 28 x 43 x 42			
	(XL) 11.4 x 17.3 x 16.5 / 29 x 44 x 42			
CASE WEIGHT	S	M	L	XL
	26.4 lbs / 12 kg	28.6 lbs / 13 kg	30.8 lbs / 14 kg	33.0 lbs / 15 kg
COO	China			

BARCODES

ITEM	BAG	DOZEN	CASE
■ 77-238/S	---	01616314009587	02616314009587
■ 77-238/M	---	01616314009594	02616314009594
■ 77-238/L	---	01616314009600	02616314009600
■ 77-238/XL	---	01616314009617	02616314009617



DIMENSIONS (in/cm)

	S	M	L	XL
A	9.25 / 23.5	9.75 / 24.7	10.25 / 26	10.75 / 27.3
B	4.6 / 11.7	4.9 / 12.3	5.1 / 13	5.4 / 13.6
H	■ Red	■ Green	■ Brown	■ Blue

Leather thickness: 1.0 (+/- 0.1) mm

