



SPECIFICATION SHEET

910-P775



SMOKESHOW™ STRUCTURAL FIREFIGHTING GLOVE

- Certified to NFPA 1971 requirements
- Elk skin back offers superior protection, thermal resistance and good grip
- Split cowhide palm offers protection, abrasion resistance, and remains soft after repeated use and laundering
- Kangaroo knuckles offers unparalleled protection, excellent abrasion resistance and minimal water absorption
- Kangaroo fourchettes on all sides of every finger and thumb from cuff to cuff for superior comfort
- 65% Nomex® / 35% Kevlar® liner
- Stitched with Kevlar® adding strength and burn resistance
- Formed knuckle guard for better flexibility, grip and less hand fatigue
- Fingertips are rounded like your actual fingers, not squared off
- Heavy duty 1/2" elastic sewn zip-zag around the entire glove at wrist
- PYRO-PRO™ insert for dexterity in the palm and added thermal protection on the back of the hand

APPLICATIONS

- Structural firefighting

TECHNICAL DATA

MATERIAL	Liner - 35% Kevlar® / 65% Nomex® Back - Elk skin Palm - Black Eversoft split cowhide			
COLOR	■ Black			
CUFF STYLE	Elastic Slip-on			
SIZES	S - XL			
PACKAGING	12 pairs per case			
CASE	12" x 12" x 12" / 30.5cm x 30.5cm x 30.5cm			
CASE WEIGHT	S	M	L	XL
	9.84 lbs / 4.46 kg	10.56 lbs / 4.8 kg	11.04 lbs / 5 kg	11.52 lbs / 5.2 kg
COO	USA			
HARM CODE	4203.29.1800US			

BARCODES

ITEM	EACH	DOZEN	CASE
■ 910-P775/S	616314158612	---	02616314158610
■ 910-P775/M	616314158629	---	02616314158627
■ 910-P775/L	616314157455	---	02616314157453
■ 910-P775/XL	616314158636	---	02616314158634



DIMENSIONS (in/cm)

	S	M	L	XL
A	9.5 / 24	10 / 25.4	10.5 / 26.67	11 / 27.9
B	4.75 / 12	5 / 12.7	5 / 12.7	5.125 / 13

