



SPECIFICATION SHEET

9150-52850



ARC HOOD, LENS, BRACKET & HARD HAT – 40 CAL/CM²

- Arc rating: ATPV 40 cal/cm²
- PPE 4 (HRC 4)
- Incorporates UV and IR absorbing ARC shield lens providing protection up to 40 cal/cm² (replaceable)
- Green tint window is coated with a permanent anti-fog inner surface
- Lens is extended 3" from face to accommodate respiratory protection and help minimize lens fogging
- Lens meets ANSI Z87.1
- Supplied with dielectric safety helmet and hard hat adapter

STANDARDS MET

- NFPA 70E 2012
- ASTM F1506-2010a
- OSHA 29 CFR1910.269

APPLICATIONS

- Electrical & utilities
- Petrochemical, gas & oil
- Mining
- Welding
- Emergency services

CARE INSTRUCTIONS

Hood: Machine wash warm, 165°F max. Tumble dry low. Do not bleach. Do not use fabric softener. Do not iron.

Lens: Clean and inspect before and after use. Clean with a damp cloth unless heavily soiled. Should further cleaning be required, clean with mild soap and water, pat dry. Disassemble if required, for cleaning and inspection.

TECHNICAL DATA

MATERIAL	Westex® Ultrasoft® 88% Cotton / 12% High Tenacity Nylon
CONSTRUCTION	Two layers: 9 oz. over 13 oz.
COLOR	■ Navy
SIZES	One size
PACKAGING	1 per polybag
CASE DIMENSIONS	16" x 16" x 12" / 40.6cm x 40.6cm x 30.5cm
CASE WEIGHT	5 lbs / 2.3 kg
COO	USA

BARCODES

ITEM	BAG	BOX	CASE
■ 9150-52850	616314137983	01616314137982	02616314137981



DIMENSIONS (in)

	ONE SIZE	
A	32	

