

ClickShare CS-100

Stand-alone wireless presentation system for small meeting rooms



Successful meetings are all about confidence. Confidence in the ideas, confidence in the presentations, but also confidence in the meeting room technology. That is why Barco has developed ClickShare. With this wireless presentation system, users can simply share what's on their laptop or mobile device, on the presentation screen. No cables, no set-up, no waiting to join in.

Sharing as a basic need

The CS-100 brings the ClickShare experience to small meeting and huddle rooms where sharing content from a laptop or mobile device is a basic need. Anyone – including guests – can connect with one click and share right away, without the need for any training. Users simply plug a USB-powered device – the ClickShare Button – into their PC or Mac and click the button to get the content from their laptop on the large meeting room screen. With the ClickShare App, users can also share content from their mobile phones or tablets.

A stand-alone model

The CS-100 is a stand-alone model with an HDMI output, that allows up to 8 users to connect and, with one user sharing at a time. The CS-100 includes the standard ClickShare security features including encryption, login management, https and the possibility to hide the SSID of the Base Unit's wireless network.

Product specifications

ClickShare CS-100

General specifications	
Operating system	Windows 7/8/8.1/10 32 & 64 bit Mac OSX 10.10/10.11/10.12 (Sierra) Android v5 & v6 (ClickShare app) iOS 8, 9 & 10(ClickShare app)
Video outputs	1x HDMI
Frame rate	Up to 30 fps
Output resolution	1920x1200
Noise Level	Fanless
Number of sources simultaneous on screen	1
Number of simultaneous connections	8
Audio	Via HDMI, analog via Audio Jack 3.5mm
iPad, iPhone and Android compatibility	Sharing of documents, browser, camera for both Android and iOS devices ClickShare app
Extended desktop	Available (depending on the driver of your graphics card)
Authentication protocol	WPA2-PSK in stand alone mode
Wireless transmission protocol	IEEE 802.11 a/g/n
Reach	Adjustable with signal strength modulation; max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit
Frequency band	2.4 GHz and 5 GHz (DFS channels not supported)
Connections	1x Ethernet LAN 1x (back) + 1x (front) USB Audio analog line out on mini jack socket (3.5mm)
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Certifications	FCC/CE
Warranty	3 years standard
ClickShare Base Unit dimensions	
Dimensions (HxWxD)	205mm x 115mm x 45mm (Min.) / 8.1" x 4.5" x 1.8" (Min.)
Power consumption	Operation: 6W (typical) / 18W (max) Standby: 2.6W (ECO standby) / 0.4W (Deep standby)
Weight	600g / 1.32lbs