

ClickShare CSE-200

Wireless presentation system for small to medium sized meeting rooms



Creativity is one of the core assets of your organization. With ClickShare, you can make sure ideas receive the attention they deserve. This wireless presentation system allows users to simply share what's on their laptop or mobile device, on the presentation screen. No cables, no set-up, no waiting to join in.

Plug in to stand out

The CSE-200 offers the ClickShare experience for small and medium-sized meeting rooms. Anyone – including guests – can connect with one click and share right away, without the need for any training. Users simply plug a USB-powered device – the ClickShare Button – into their PC or Mac and click the button to get the content from their laptop on the large meeting room screen. With the ClickShare App, users can also share content from their mobile phones or tablets.

Encouraging collaboration

The CSE-200 was designed for enterprise rollouts and offers enhanced security features, a wider range of connectivity options – including AirPlay and Google Cast support for non-HDCP content – and central management. Allowing up to 2 persons to share content simultaneously, the CSE-200 ensures direct connectivity to the central screen and encourages collaboration. For user convenience, security features of the CSE-200 can be set to one of three predefined levels, depending on the company's policies and needs. Last but not least, the device's API also makes integration into the company network a lot easier.

Product specifications

ClickShare CSE-200

General specifications	
AirPlay Support	iOS mirroring (AirPlay) from iOS 9.0 up to iOS 10.3 / Mac OS 10.11 El Capitan or higher
Operating system	Windows 7/8/8.1/10 32 & 64 bit Mac OSX 10.10/10.11/10.12 (Sierra) Android v5 & v6 (ClickShare app) iOS 8, 9 & 10 (ClickShare app)
Video outputs	1x HDMI
Frame rate	Up to 30 fps
Output resolution	1920x1200
Noise Level	Fanless
Number of sources simultaneous on screen	2
Number of simultaneous connections	16
Audio	Via HDMI, analog via Audio Jack 3.5mm, S/PDIF
iPad, iPhone and Android compatibility	Sharing of documents, browser, camera for both Android and iOS devices via ClickShare app
Extended desktop	Available (depending on the driver of your graphics card)
Authentication protocol	WPA2-PSK in stand alone mode WPA2-PSK or IEEE 802.1X in network integration mode
Wireless transmission protocol	IEEE 802.11 a/g/n
Reach	Adjustable with signal strength modulation; max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit
Frequency band	2.4 GHZ and 5 GHz (DFS channels not supported)
Connections	1x Ethernet LAN 2x (back) + 1x (front) USB Audio analog line out on mini jack socket (3.5mm), digital S/PDIF
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Certifications	FCC/CE
Warranty	3 years standard Possible to extend to 5 years
ClickShare Base Unit dimensions	
Dimensions (HxWxD)	205mm x 115mm x 45mm (excl. antennas) / 8.1" x 4.5" x 1.8" 205mm x 150mm x 135mm (incl. antennas) / 8.1" x 5.9" x 5.3"
Power supply	Standard 110/220 V AC plug or Power over Ethernet (PoE Plus)
Power consumption	Operation: 6W (typical) / 18W (max) Standby: 2.6W (ECO standby) / 0.4W (Deep standby)
Weight	600g / 1.32lbs