

Forwarding Rate: 64-Byte L3 Packets	
Cisco Catalyst 2960X-24PS-L	71.4 Mpps
Cisco Catalyst 2960X-24PSQ-L	71.4 Mpps
Cisco Catalyst 2960X-48TS-L	107.1 Mpps
Cisco Catalyst 2960X-24TS-L	71.4 Mpps
Cisco Catalyst 2960X-48TS-LL	104.2 Mpps
Cisco Catalyst 2960X-24TS-LL	68.5 Mpps
Catalyst 2960-XR Family	
Cisco Catalyst 2960XR-48FPD-I	130.9 Mpps
Cisco Catalyst 2960XR-48LPD-I	130.9 Mpps
Cisco Catalyst 2960XR-24PD-I	95.2 Mpps
Cisco Catalyst 2960XR-48TD-I	130.9 Mpps
Cisco Catalyst 2960XR-24TD-I	95.2 Mpps
Cisco Catalyst 2960XR-48FPS-I	107.1 Mpps
Cisco Catalyst 2960XR-48LPS-I	107.1 Mpps
Cisco Catalyst 2960XR-24PS-I	71.4 Mpps
Cisco Catalyst 2960XR-48TS-I	107.1 Mpps
Cisco Catalyst 2960XR-24TS-I	71.4 Mpps

Table 13. Cisco Catalyst 2960-X Series Mechanical Specifications

Models		
Dimensions	Inches (H x D x W)	Centimeters (H x D x W)
WS-C2960X-48FPD-L	1.75 x 14.5 x 17.5	4.5 x 36.8 x 44.5
WS-C2960X-48LPD-L	1.75 x 14.5 x 17.5	4.5 x 36.8 x 44.5
WS-C2960X-48TD-L	1.75 x 11.0 x 17.5	4.5 x 27.9 x 44.5
WS-C2960X-24PD-L	1.75 x 14.5 x 17.5	4.5 x 36.8 x 44.5
WS-C2960X-24TD-L	1.75 x 11.0 x 17.5	4.5 x 27.9 x 44.5
WS-C2960X-48FPS-L	1.75 x 14.5 x 17.5	4.5 x 36.8 x 44.5
WS-C2960X-48LPS-L	1.75 x 14.5 x 17.5	4.5 x 36.8 x 44.5
WS-C2960X-48TS-L	1.75 x 11.0 x 17.5	4.5 x 27.9 x 44.5
WS-C2960X-24PS-L	1.75 x 14.5 x 17.5	4.5 x 36.8 x 44.5
WS-C2960X-24PSQ-L	1.73 x 11.03 x 17.5	4.45 x 28.0 x 44.5
WS-C2960X-24TS-L	1.75 x 11.0 x 17.5	4.5 x 27.9 x 44.5
WS-C2960X-48TS-LL	1.75 x 11.0 x 17.5	4.5 x 27.9 x 44.5
WS-C2960X-24TS-LL	1.75 x 11.0 x 17.5	4.5 x 27.9 x 44.5
Weights	Pounds	Kilograms
WS-C2960X-48FPD-L	12.9 lbs	5.8 Kg
WS-C2960X-48LPD-L	12.9 lbs	5.8 Kg
WS-C2960X-48TD-L	9.6 lbs	4.3 Kg
WS-C2960X-24PD-L	12.7 lbs	5.7 Kg
WS-C2960X-24TD-L	8.9 lbs	4.0 Kg
WS-C2960X-48FPS-L	12.9 lbs	5.8 Kg
WS-C2960X-48LPS-L	12.9 lbs	5.8 Kg
WS-C2960X-48TS-L	9.4 lbs	4.2 Kg