

POWER UNITS & ATTACHMENTS SELECTION TOOL

SELECT A POWER UNIT

	PP500	PP600	PP650	VX1000/C
Motor Performance (Power): Air Watts	500	600	650	1040
Filtration				
Regular: Cleaner indoor air than with a portable vacuum	●	●	●	●
Sealed HEPA: Cleaner indoor air than most central vacuums		●	●	
Sealed HEPA 2.0: Dual HEPA filters for the cleanest indoor air			●	
What cleaning system do you prefer?				
Bagged	●	●	●	VX1000
Bagless		●	●	VX1000C
Hybrid (bagged & bagless)		●	●	
Where will it be installed?				
Garage	●	●	●	●
Closet	●	●	●	
Basement	●	●	●	●
House Size				
1,000 to 4,000 square feet	●	●	●	●
2,000 to 7,000 square feet		●	●	●
2,500 to 10,000 square feet			●	●
3,500 to 15,000 square feet				●

SELECT AN ATTACHMENT SET

	CS100	CS200	CS300	CS400	CS500	CS600
What type of flooring do you have?						
Hard floor		●	●	●	●	●
Carpet		●		●	●	●
Thick carpet					●	●
Where do you want to use your vacuum?						
Garage/car	●					
Inside the house		●	●	●	●	●
What type of inlets do you have?						
Current Carrying (Electric Driven for faster/easier clean)					●	●
Standard (Air Driven)	●	●	●	●	●	
Are you looking for a new way to groom your pets?						
Yes				●		

NUTONE VX POWER UNIT... QUALITY FROM TOP TO BOTTOM



(Bagless version shown)

VX1000/VX1000C



Air filtration with **HEPA®** and anti-stick technology (VX1000C).



VX1000C
Cyclonic model



1040
Air Watts
from two powerful
240 volt motors



VX1000
Bagged model



8 year warranty

- Easy-to-clean cyclonic filter accessible through door panel returns it to new status (VX1000C)
- State-of-the-art control board gives timed fill indicators for cyclonic unit (VX1000C)
- Built in sound suppression greatly reduces motor noise
- Left and right intake for flexible installation
- Oval shape for space saving mounting
- 7 gallon debris pail with easy on/off snap release and integrated site glass to check fill level
- Bag-full indicator light (VX1000)
- For homes 3,500 to 15,000 sq. ft.
- Made in North America



ATTACHMENT SETS



CS600

Carpet & Bare Floor Combination Electric Direct Connect Attachment Set

- CT105 – Natural Hair Dusting Brush
- CT110 – Long Crevice Tool
- CT106G – Natural Hair Upholstery Tool
- CK135 – Ratcheting Wand
- CT158 – Premium Twist & Turn Floor Brush
- CT175 – Current Carrying Ratcheting Wand
- CT700 – Deluxe Electric Powerhead
- CH615 – Current Carrying Direct Connect Crushproof Hose
- CA130 – Hose Sock
- Hose Hanger
- Wand Hanger
- Mesh Storage Bag



CS500

Carpet & Bare Floor Combination Electric Pigtail Attachment Set

- CT105 – Natural Hair Dusting Brush
- CT110 – Long Crevice Tool
- CT106G – Natural Hair Upholstery Tool
- CK135 – Ratcheting Wand
- CT158 – Premium Twist & Turn Floor Brush
- CT175 – Current Carrying Ratcheting Wand
- CT700 – Deluxe Electric Powerhead
- CH515 – Current Carrying Pigtail Crushproof Hose
- CA130 – Hose Sock
- Hose Hanger
- Wand Hanger
- Mesh Storage Bag



CS400

Carpet & Bare Floor Combination Air Turbine Pet Care Attachment Set

- CT105 – Natural Hair Dusting Brush
- CT110 – Long Crevice Tool
- CT106G – Natural Hair Upholstery Tool
- CK135 – Ratcheting Wand
- CT158 – Premium Twist & Turn Floor Brush
- CT350B – Air Turbine Brush
- CT109 – Pet Brush
- CH235 – 30' Crushproof Hose
- CA130 – Hose Sock
- Hose Hanger
- Wand Hanger
- Mesh Storage Bag



CS300

Bare Floor Attachment Set

- CT105 – Natural Hair Dusting Brush
- CT110 – Long Crevice Tool
- CT106G – Natural Hair Upholstery Tool
- CK135 – Ratcheting Wand
- CT158 – Premium Twist & Turn Floor Brush
- CH235 – 30' Crushproof Hose
- CA130 – Hose Sock
- Hose Hanger
- Wand Hanger
- Mesh Storage Bag