

710CS/LS and 7109CS/LS Series - Continuous Piezo Sounder

Model Number	Part Number	Voltage	Wall Mount	Ceiling Mount	9 Foot Line Cord	Interconnect Up To 6 Units	Form C Contacts	9VDC Battery Back-Up
710CS-W	907-0231-002	120VAC	●			●	●	
710CS-C	907-0232-002	120VAC		●		●	●	
710CSX-W	907-0235-002	120VAC	●			●	●	
710CSX-C	907-0236-002	120VAC		●		●	●	
710LS	907-0239-002	120VAC	●		●			
7109CS-W	917-0007-002	120VAC	●			●	●	●
7109CS-C	917-0008-002	120VAC		●		●	●	●
7109CSX-W	917-0010-002	120VAC	●			●	●	●
7109CSX-C	917-0011-002	120VAC		●		●	●	●
7109LS	917-0006-002	120VAC	●		●			●

713CS/LS and 7139CS/LS Series - Temporal 3 Piezo Sounder

Model Number	Part Number	Voltage	Wall Mount	Ceiling Mount	9 Foot Line Cord	Interconnect Up To 6 Units	Form C Contacts	9VDC Battery Back-Up
713CS-W	907-0248-002	120VAC	●			●	●	
713CS-C	907-0249-002	120VAC		●		●	●	
713CSX-W	907-0252-002	120VAC	●			●	●	
713CSX-C	907-0253-002	120VAC		●		●	●	
713LS	907-0256-002	120VAC	●		●			
7139CS-W	917-0019-002	120VAC	●			●	●	●
7139CS-C	917-0020-002	120VAC		●		●	●	●
7139CSX-W	917-0021-002	120VAC	●			●	●	●
7139CSX-C	917-0022-002	120VAC		●		●	●	●
7139LS	917-0018-002	120VAC	●		●			●

NOTES

- Available in square configuration only.
- Line cord models not available for ceiling mount applications, wall mount only
- The CSX models have the ability to turn its strobe on from a field mounted relay
- When testing 713/7139 units, it may take up to 16 seconds longer for smoke alarm to go in or out of alarm mode.
- It is recommended that 710/713/7109/7139 Series smoke alarm be tested weekly
- Refer to Technical Bulletin 002 for Easy Wash® on site washing instructions
- 710/7109 units produce a non-temporal audible alarm and are therefore not intended for locations where the desired action of the occupant(s) is evacuation
- 713/7139 units produce a temporal 3 audible alarm. Per NFPA 72, the American National Standard Audible Emergency Evacuation Signal as defined in ANSI S3.41, is required whenever the intended response is to evacuate the building
- Candela rating is a 177 candela strobe light listed to ANSI/UL 1971 listed strobe light
- Flash rate per minute: 60 minimum

“W” = Wall Mount

“C” = Ceiling Mount