

Cube Hotswap Series

More options and added storage space, all in a compact size

Processors	i3	i5	i7
IP Inputs	Up to 16	Up to 32	Up to 32
Included IP Licenses	32 channels of GeoVision IP cameras		
3rd Party IP Licenses	Optional		
Server OS	Windows 7 Pro 64 Bit embedded		
OS Drive	64GB SSD		
Optional OS Drive	128GB SSD		
Data HDD Included	0		
Max # of HDD	4		
Max HDD Storage	16TB		
Removable HDD	Yes		
Hotswappable HDD	Yes		
Height (in)	7.5		
Width (in)	7.75		
Depth (in)	10		
Weight Approximate (lbs)	10 without HDDs		
NIC	2 (1 Internal, 1 External)		
RAM	8GB		
USB Ports	6		
VGA Output	2 (VGA, DVI, HDMI)		
Hardware Watchdog	Included		
Operating Temperature	0 to 45 °C (32 to 133 °F)		
Humidity	0 to 80% RH (non condensing)		

