

111-00965

# HellermannTyton

Article Number: 111-00965



Description: Heavy-Duty Cable Tie, 21" Long, UL Rated, 175lb Tensile Strength, PA46, Brown, 25/pkg

|                    |                                     |                                                                                                                                                                                                                                                                                                 |
|--------------------|-------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Base Data          |                                     |                                                                                                                                                                                                                                                                                                 |
|                    | Local Order Number                  | 111-00965                                                                                                                                                                                                                                                                                       |
|                    | Type                                | T150M                                                                                                                                                                                                                                                                                           |
|                    | Color                               | Brown (BN)                                                                                                                                                                                                                                                                                      |
|                    | Features and benefits               | <ul style="list-style-type: none"> <li>• Cable ties made of PA46 material provide a greater resistance to high heat exposures than PA66 heat stabilized material.</li> <li>• Head design provides high tensile strength with very low insertion force.</li> </ul>                               |
|                    | Product Description                 | HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation. |
|                    | Short Description                   | Heavy-Duty Cable Tie, 21" Long, UL Rated, 175lb Tensile Strength, PA46, Brown, 25/pkg                                                                                                                                                                                                           |
| Product Dimensions |                                     |                                                                                                                                                                                                                                                                                                 |
|                    | Minimum Tensile Strength (Imperial) | 175.0lbs                                                                                                                                                                                                                                                                                        |
|                    | Minimum Tensile Strength (Metric)   | 780.0N                                                                                                                                                                                                                                                                                          |
|                    | Length L (Imperial)                 | 21.0"                                                                                                                                                                                                                                                                                           |
|                    | Length L (Metric)                   | 530.0mm                                                                                                                                                                                                                                                                                         |
|                    | Fixation Method                     | None                                                                                                                                                                                                                                                                                            |
|                    | Identification Plate Position       | none                                                                                                                                                                                                                                                                                            |
|                    | Releasable Closure                  | No                                                                                                                                                                                                                                                                                              |
|                    | Tie Closure                         | plastic pawl                                                                                                                                                                                                                                                                                    |
|                    | Variant                             | Inside Serrated                                                                                                                                                                                                                                                                                 |
|                    | Width W (Imperial)                  | 0.35"                                                                                                                                                                                                                                                                                           |
|                    | Width W (Metric)                    | 8.9mm                                                                                                                                                                                                                                                                                           |
|                    | Bundle Diameter Min. (Imperial)     | 0.32"                                                                                                                                                                                                                                                                                           |
|                    | Bundle Diameter Min. (Metric)       | 8.0mm                                                                                                                                                                                                                                                                                           |
|                    | Bundle Diameter Max. (Imperial)     | 5.9"                                                                                                                                                                                                                                                                                            |
|                    | Bundle Diameter Max. (Metric)       | 150.0mm                                                                                                                                                                                                                                                                                         |

111-00965



|                             |                             |                                   |
|-----------------------------|-----------------------------|-----------------------------------|
| Product Dimensions          | Thickness T (Metric)        | 1.9mm                             |
| Material and Specifications |                             |                                   |
|                             | Material                    | Polyamide 4.6 (PA46)              |
|                             | Material Shortcut           | PA46                              |
|                             | Flammability                | UL 94 V2                          |
|                             | Halogenfree                 | Yes                               |
|                             | Operating Temperature       | -40°F to +275°F (-40°C to +135°C) |
|                             | ROHS Compliant              | Yes                               |
| Logistic and Packaging      |                             |                                   |
|                             | Package Quantity (Imperial) | 25                                |
|                             | Package Quantity (Metric)   | 25                                |
|                             | Customs Number(Schedule B)  | 3926909987                        |