

111-01933

HellermannTyton

Article Number: 111-01933

Description: Standard Cable Tie, 4" Long, UL Rated, 18lb Tensile Strength, PA66, Brown, 100/pkg



Base Data		
	Local Order Number	111-01933
	Type	T18R
	Color	Brown (BN)
	Features and benefits	• Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
	Quantity Per	bag
	Product Description	T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
	Short Description	Standard Cable Tie, 4" Long, UL Rated, 18lb Tensile Strength, PA66, Brown, 100/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	18.0lbs
	Minimum Tensile Strength (Metric)	80.0N
	Length L (Imperial)	4.0"
	Length L (Metric)	100.0mm
	Fixation Method	None
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	0.1"
	Width W (Metric)	2.45mm
	Bundle Diameter Min. (Imperial)	0.06"
	Bundle Diameter Min. (Metric)	1.5mm
	Bundle Diameter Max. (Imperial)	0.86"

111-01933



Product Dimensions	Bundle Diameter Max. (Metric)	22.0mm
	Thickness T (Metric)	1.0mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100Pieces
	Customs Number(Schedule B)	3926909987