

111-15302

HellermannTyton



Article Number: 111-15302

Description: Heavy-Duty Cable Tie, 52.2" Long, UL Rated, 175lb Tensile Strength, PA66, Yellow, 25/pkg

Base Data		
	Local Order Number	T150XLL4X2
	Type	T150XLL
	Color	Yellow (YE)
	Features and benefits	• Heavy duty design to offer higher tensile strength. • Head design provides high tensile strength with very low insertion force.
	Quantity Per	bag
	Product Description	HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
	Short Description	Heavy-Duty Cable Tie, 52.2" Long, UL Rated, 175lb Tensile Strength, PA66, Yellow, 25/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	175.0lbs
	Minimum Tensile Strength (Metric)	780.0N
	Length L (Imperial)	52.2"
	Length L (Metric)	1325.0mm
	Fixation Method	None
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	0.35"
	Width W (Metric)	8.9mm
	Bundle Diameter Min. (Imperial)	6.0"
	Bundle Diameter Min. (Metric)	152.0mm
	Bundle Diameter Max. (Imperial)	16.0"
	Bundle Diameter Max. (Metric)	405.0mm

111-15302



Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	ROHS Compliant	Yes
	Certification/Specification	UL ANSI/UL 62275
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	25
	Package Quantity (Metric)	25
	Customs Number(Schedule B)	3926909987