

111-81910

HellermannTyton

Article Number: 111-81910



Description: Identification Tie, 4.3" Long, 18lb Tensile Strength, PA66, Black, 100/pkg

Base Data		
	Local Order Number	IT18FL0C2
	Type	IT18FL
	Color	Black (BK)
	Features and benefits	• Identification plate feature allows bundles to be easily marked and identified. • Wire and cable harnesses can be secured and identified using just one product, which saves time. • Plates can be marked manually with a permanent marker or with a pre-printed adhesive label.
	Quantity Per	bag
	Product Description	Identification Cable Ties feature an identification plate that allows wire and cable bundles to be easily marked and identified. These ties enable wire and cables to be secured and identified using just one product, saving installation time. The plates can be marked using a permanent marker or with a HellermannTyton adhesive label.
	Short Description	Identification Tie, 4.3" Long, 18lb Tensile Strength, PA66, Black, 100/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	18.0lbs
	Minimum Tensile Strength (Metric)	80.0N
	Length L (Imperial)	4.3"
	Length L (Metric)	110.0mm
	Fixation Method	None
	Identification Plate Position	stands of bundle
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	0.81"
	Width W (Metric)	20.5mm
	Width W2 (Imperial)	0.1"
	Width W2 (Metric)	2.5mm
	Height H (Imperial)	.35"

111-81910



Product Dimensions	Height H (Metric)	9.0mm
	Bundle Diameter Min. (Imperial)	0.06"
	Bundle Diameter Min. (Metric)	1.5mm
	Bundle Diameter Max. (Imperial)	0.75"
	Bundle Diameter Max. (Metric)	19.0mm
	Outside Diameter Min. (Imperial)	0.059"
	Outside Diameter Min. (Metric)	1.50mm
	Outside Diameter Max. (Imperial)	0.75"
	Outside Diameter Max. (Metric)	19.00mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces
	Weight (Metric)	0.3kg