

111-85204

HellermannTyton



Article Number: 111-85204

Description: Identification Tie, 8" Long, 50lb Tensile Strength, PA66, Red, 50/plain pkg

Base Data		
	Local Order Number	IT50RD2K3
	Type	IT50RD
	Color	Red (RD)
	Features and benefits	• Identification plate feature allows bundles to be easily marked and identified. • Wire and cable harnesses can be secured and identified using just one product, which saves time. • Plates can be marked manually with a permanent marker or with a pre-printed adhesive label.
	Quantity Per	bag
	Product Description	Identification Cable Ties feature an identification plate that allows wire and cable bundles to be easily marked and identified. These ties enable wire and cables to be secured and identified using just one product, saving installation time. The plates can be marked using a permanent marker or with a HellermannTyton adhesive label.
	Short Description	Identification Tie, 8" Long, 50lb Tensile Strength, PA66, Red, 50/plain pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	50.0lbs
	Minimum Tensile Strength (Metric)	225.0N
	Length L (Imperial)	8.0"
	Length L (Metric)	205.0mm
	Fixation Method	None
	Identification Plate Position	attached to bundle
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	1.1"
	Width W (Metric)	29.0mm
	Width W2 (Imperial)	0.19"
	Width W2 (Metric)	4.7mm
	Height H (Imperial)	1.04"

111-85204



Product Dimensions	Height H (Metric)	26.3mm
	Bundle Diameter Min. (Imperial)	0.4"
	Bundle Diameter Min. (Metric)	10.0mm
	Bundle Diameter Max. (Imperial)	1.7"
	Bundle Diameter Max. (Metric)	44.0mm
	Outside Diameter Min. (Imperial)	0.393"
	Outside Diameter Min. (Metric)	10.00mm
	Outside Diameter Max. (Imperial)	1.73"
	Outside Diameter Max. (Metric)	44.00mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	US MILSPEC	MS3368-3-2C
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	ROHS Compliant	Yes
	Certification/Specification	CAGE Code 53421
	UL Recognized (US)	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	50
	Package Quantity (Metric)	50
	Customs Number(Schedule B)	3926909987