

111-85300

Article Number: 111-85300

Description: Identification Tie, 15.4" Long, 50lb Tensile Strength, PA66, Orange, 100/pkg



Base Data	Local Order Number	IT50L3C2
	Type	IT50L
	Color	Orange (OG)
	Features and benefits	<ul style="list-style-type: none"> <li>• Identification plate feature allows bundles to be easily marked and identified.</li> <li>• Wire and cable harnesses can be secured and identified using just one product, which saves time.</li> <li>• Plates can be marked manually with a permanent marker or with a pre-printed adhesive label.</li> </ul>
	Quantity Per	bag
	Product Description	Identification Cable Ties feature an identification plate that allows wire and cable bundles to be easily marked and identified. These ties enable wire and cables to be secured and identified using just one product, saving installation time. The plates can be marked using a permanent marker or with a HellermannTyton adhesive label.
	Short Description	Identification Tie, 15.4" Long, 50lb Tensile Strength, PA66, Orange, 100/pkg
	Product Dimensions	Minimum Tensile Strength (Imperial)
Minimum Tensile Strength (Metric)		225.0N
Length L (Imperial)		15.4"
Length L (Metric)		390.0mm
Fixation Method		None
Identification Plate Position		attached to bundle
Tie Closure		plastic pawl
Variant		Inside Serrated
Width W (Imperial)		2.2"
Width W (Metric)		56.0mm
Width W2 (Imperial)		0.19"
Width W2 (Metric)		4.7mm
Height H (Imperial)		.50"

111-85300



Product Dimensions	Height H (Metric)	12.80mm
	Bundle Diameter Min. (Imperial)	0.75"
	Bundle Diameter Min. (Metric)	19.0mm
	Bundle Diameter Max. (Imperial)	3.9"
	Bundle Diameter Max. (Metric)	100.0mm
	Outside Diameter Min. (Imperial)	0.75"
	Outside Diameter Min. (Metric)	19.00mm
	Outside Diameter Max. (Imperial)	3.94"
	Outside Diameter Max. (Metric)	100.00mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	US MILSPEC	SAE-AS33681
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	ROHS Compliant	Yes
	Certification/Specification	CAGE Code 53421
	UL Recognized (US)	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100