

120-04401



Article Number: 120-04401

Description: Cable Tie for AT2000, 18 lb Tensile Strength, PA66VO, White, 50/bandolier, 500/pkg



Base Data		
	Local Order Number	T18RA50VO
	Type	T18RA50
	Color	White (WH)
	Features and benefits	- The AT2000 cable tie system is designed for automatic installation on bundles up to .75" and a minimum tensile strength of 18 lbs. - Available in reels of 5,000 each or bandoliers of 50 each.
	Quantity Per	bag
	Product Description	HellermannTyton offers the widest range of automatic cable tie tool systems which cover cable tie tensile strengths of 18, 30, and 50 pounds with bundle diameters between 1/16" to over 3". For use with HellermannTyton's Automatic Tool Systems.
	Technical Description	Cable Tie for AT2000, White, 50/bandolier
	Short Description	Cable Tie for AT2000, 18 lb Tensile Strength, PA66VO, White, 50/bandolier, 500/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	18.0lbs
	Minimum Tensile Strength (Metric)	80.0N
	Length L (Imperial)	4.0"
	Length L (Metric)	4.8mm
	Power Supply unit	Electrical
	Tie Closure	plastic pawl
	Width W (Imperial)	0.1"
	Width W (Metric)	2.5mm
	Bundle Diameter Min. (Imperial)	0.03"
	Bundle Diameter Min. (Metric)	0.7mm
	Bundle Diameter Max. (Imperial)	0.75"
	Bundle Diameter Max. (Metric)	20.0mm
	Thickness T (Imperial)	0.043"
	Thickness T (Metric)	1.1mm

120-04401



Material and Specifications		
	Material	Polyamide 6.6 V0 (PA66V0)
	Material Shortcut	PA66V0
	Flammability	UL 94 V0
	Halogenfree	Yes
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	ROHS Compliant	Yes
	Certification/Specification	UL ANSI/UL 1565
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500
	Package Quantity (Metric)	500Pieces
	Customs Number(Schedule B)	3926909987