

120-05015

HellermannTyton



Article Number: 120-05015

Description: Cable Tie for AT2000, 18lb Tensile Strength, PA46, Natural, 5000/reel

Base Data		
	Local Order Number	120-05015
	Type	T18RA5000
	Color	Natural (NA)
	Features and benefits	• The AT2000 cable tie system is designed for automatic installation on bundles up to .75" and a minimum tensile strength of 18 lbs. • Available in reels of 5,000 each or bandoliers of 50 each.
	Quantity Per	reel
	Product Description	HellermannTyton offers the widest range of automatic cable tie tool systems which cover cable tie tensile strengths of 18, 30, and 50 pounds with bundle diameters between 1/16" to over 3". For use with HellermannTyton's Automatic Tool Systems.
	Technical Description	Cable Tie for AT2000, Natural
	Short Description	Cable Tie for AT2000, 18lb Tensile Strength, PA46, Natural, 5000/reel
Product Dimensions		
	Minimum Tensile Strength (Imperial)	18.0lbs
	Minimum Tensile Strength (Metric)	80.0N
	Length L (Imperial)	4.0"
	Length L (Metric)	4.8mm
	Power Supply unit	Electrical
	Tie Closure	plastic pawl
	Width W (Imperial)	0.1"
	Width W (Metric)	2.5mm
	Bundle Diameter Min. (Imperial)	0.03"
	Bundle Diameter Min. (Metric)	0.7mm
	Bundle Diameter Max. (Imperial)	0.75"
	Bundle Diameter Max. (Metric)	20.0mm

120-05015



Material and Specifications		
	Material	Polyamide 4.6 (PA46)
	Material Shortcut	PA46
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +275°F (-40°C to +135°C)
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	5000
	Package Quantity (Metric)	5000
	Customs Number(Schedule B)	3926909987