

126-00015

HellermannTyton



Article Number: 126-00015

Description: Domed Push Mount Tie, 6.3" Long, Fixing Hole Diameter .24" - .48", PA66HS, Black, 500/pkg

Base Data		
	Local Order Number	126-00015
	Type	T50SDOP
	Color	Black (BK)
	Features and benefits	• Part is easy to install without the need for a tool. • Design provides low insertion and high extraction force. • The oval design helps prevent the part from twisting.
	Quantity Per	bag
	Product Description	HellermannTyton's dome push in tie with arrowhead locks into place between the fixing and the head of the cable tie. This covers the hole and minimizes the ingress of dust, dirt, and water. The anchor adjusts for variations in panel thickness, which ensures a secure fixing at all times. The oval design helps prevent the part from twisting.
	Short Description	Domed Push Mount Tie, 6.3" Long, Fixing Hole Diameter .24" - .48", PA66HS, Black, 500/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	50.0lbs
	Minimum Tensile Strength (Metric)	225N
	Length L (Imperial)	6.3"
	Length L (Metric)	160.0mm
	Fixation Method	Arrowhead for oval holes
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	0.2"
	Width W (Metric)	5.0mm
	Height H (Imperial)	0.36"
	Bundle Diameter Min. (Imperial)	0.2"
	Bundle Diameter Min. (Metric)	5.0mm

126-00015



Product Dimensions	Bundle Diameter Max. (Imperial)	1.2"
	Bundle Diameter Max. (Metric)	30.0mm
	Disc Diameter (Imperial)	0.87"
	Disc Diameter (Metric)	22.0mm
	Panel Thickness Max. (Imperial)	0.08"
	Panel Thickness Max. (Metric)	1.9mm
	Panel Thickness Min. (Imperial)	0.04"
	Panel Thickness Min. (Metric)	1.0mm
	Mounting Hole Diameter D (Imperial)	0.24 - 0.48"
	Mounting Hole Diameter D (Metric)	6.2 x 12.2 mm
	Mounting Hole Diameter D Min. (Imperial)	0.244"
	Mounting Hole Diameter D Max. (Imperial)	0.48"
	Stud Length min (metric)	9.2mm
	Thickness T (Imperial)	0.05"
	Thickness T (Metric)	1.3mm
Material and Specifications		
	Material	Polyamide 6.6 heat stabilized (PA66HS)
	Material Shortcut	PA66HS
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500
	Package Quantity (Metric)	500Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces
	Weight (Metric)	1.7kg