

126-00065

HellermannTyton



Article Number: 126-00065

Description: Arrowhead Mount Ties with Seal, 6.5" Long, 50lb Tensile, PA66HS, Natural, 500/bag

Base Data		
	Local Order Number	126-00065
	Type	T50SOSSFT6.5E-MS-MD
	Color	Natural (NA)
	Features and benefits	One piece mounting ties offer a complete solution by both bundling cable and at the same time providing a mounting solution. HellermannTyton's one piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.
	Quantity Per	bag
	Short Description	Arrowhead Mount Ties with Seal, 6.5" Long, 50lb Tensile, PA66HS, Natural, 500/bag
Product Dimensions		
	Minimum Tensile Strength (Imperial)	50.0lbs
	Minimum Tensile Strength (Metric)	180N
	Length L (Imperial)	6.5"
	Length L (Metric)	163.0mm
	Fixation Method	Arrowhead
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Width W (Imperial)	0.18"
	Width W (Metric)	4.6mm
	Height H (Imperial)	0.63"
	Bundle Diameter Min. (Imperial)	0.06"
	Bundle Diameter Min. (Metric)	1.5mm
	Bundle Diameter Max. (Imperial)	1.4"
	Bundle Diameter Max. (Metric)	35.0mm
	Disc Diameter (Imperial)	0.63"

126-00065



Product Dimensions	Disc Diameter (Metric)	16.0mm
	Panel Thickness Max. (Imperial)	0.06"
	Panel Thickness Max. (Metric)	1.6mm
	Panel Thickness Min. (Imperial)	0.03"
	Panel Thickness Min. (Metric)	0.7mm
	Mounting Hole Diameter D (Imperial)	0.25 - 0.27"
	Mounting Hole Diameter D (Metric)	6.1 - 6.6 mm (hexagonal)
	Mounting Hole Diameter D Min. (Imperial)	0.244"
	Mounting Hole Diameter D Max. (Imperial)	0.26"
	Thickness T (Imperial)	0.05"
	Thickness T (Metric)	1.3mm
Material and Specifications		
	Material	Polyamide 6.6 heat stabilized (PA66HS)
	Material Shortcut	PA66HS
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500
	Package Quantity (Metric)	500Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces
	Weight (Metric)	1.51kg