

133-00997

HellermannTyton

Article Number: 133-00997



Description: HC Clamp Bundle Separator, Two Hole, PA66GFHIRHS, Red, 500/pkg

Base Data		
	Local Order Number	133-00997
	Type	HC2E_PA66HIRHS_GPN11-0740
	Color	Red (RD)
	Features and benefits	<ul style="list-style-type: none"> • Separates and secures bundles avoiding abrasion • Designed to handle both convoluted tubing and bundles not covered in convoluted tubing • Come in a variety of sizes and colors to be easily identified
	Quantity Per	bag
	Product Description	HC Clamps separate multiple bundles and secure them to brackets or frame rails. Each mount has two pawls for easy pre-installation on a threaded fastener prior to securing with a mechanical fastener. HC Clamps have ribs that make them ideal for convoluted tubing, but they can also be used to separate separate bundles that aren't protected with convoluted tubing.
	Short Description	HC Clamp Bundle Separator, Two Hole, PA66GFHIRHS, Red, 500/pkg
Product Dimensions		
	Length L (Imperial)	2.747"
	Length L (Metric)	67.77mm
	Width W (Imperial)	1.1"
	Width W (Metric)	27.94mm
	Height H (Imperial)	1.38"
	Height H (Metric)	34.94mm
	Bundle Diameter Max. (Imperial)	0.513"
	Bundle Diameter Max. (Metric)	13.03mm
	Mounting Hole Diameter D (Imperial)	0.32"
	Mounting Hole Diameter D (Metric)	8.12 mm
Material and Specifications		
	Material	Polyamide 6.6, high impact modified, heat stabilized, glass fiber reinforced (PA66HIRHSGF)

133-00997



Material and Specifications	Material Shortcut	PA66HIRHSGF
	Operating Temperature	-40°F to +250°F (-40°C to +121°C)
Logistic and Packaging		
	Package Quantity (Imperial)	500
	Package Quantity (Metric)	500
	Customs Number(Schedule B)	3926909987