

148-00005

HellermannTyton



Article Number: 148-00005

Description: Nail Clip, .14" Cable Diameter, PP,ST, Black, 100/pkg

Base Data		
	Local Order Number	NC3.50
	Type	NC3.5
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Hardened steel nail allows easy installation into wood, masonry joints, cinder block and mortar. • No sharp edges reduce risk of cutting cables or sheaths.
	Quantity Per	box
	Product Description	Tough, precision engineered Nail Clips hold wire and cable securely in place. The nail is made of hardened steel for driving into wood, masonry joints, cinder block, and mortar. The nail clips do not have sharp edges, which reduces the chance of cutting cable jackets or sheaths, causing signal loss. Available in white or black.
	Short Description	Nail Clip, .14" Cable Diameter, PP,ST, Black, 100/pkg
Product Dimensions		
	Length L (Imperial)	0.63"
	Length L (Metric)	16.0mm
	Width W (Imperial)	0.18"
	Width W (Metric)	4.6mm
	Width W2 (Imperial)	0.19"
	Width W2 (Metric)	4.8mm
	Height H (Imperial)	.18"
	Height H (Metric)	4.60mm
	Nominal Diameter (Imperial)	1/8"
	Nominal Diameter (Metric)	3.5mm
Material and Specifications		
	Material	Polyethylene (PE)
	Material Shortcut	ST

148-00005



Material and Specifications	Flammability	UL 94 HB
	Operating Temperature	-40°F to +239°F (-40°C to +115°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100Pieces
	Customs Number(Schedule B)	7317009000