

150-28140

HellermannTyton

Article Number: 150-28140



Description: Ladder Stud Mount, 4.3" Length, Stud Diameter .2", Max Bundle Diameter 0.91", PA66, Black, 500/pkg

Base Data		
	Local Order Number	150-28140
	Type	FBF140
	Color	Black (BK)
	Features and benefits	• Mount design applies quickly and easily to .2" (5mm) studs. • Unique latch style allows for easy re-entry to bundles. • Design gives low insertion force and high extraction force.
	Quantity Per	bag
	Product Description	Ladder Stud Mounts can be used in a wide variety of applications where .2" diameter bolts are used, and cables need to be bundled and secured. The unique latch style allows for easy re-entry to bundles.
	Short Description	Ladder Stud Mount, 4.3" Length, Stud Diameter .2", Max Bundle Diameter 0.91", PA66, Black, 500/pkg
Product Dimensions		
	Length L (Imperial)	5.7"
	Length L (Metric)	142mm
	Fixation Method	Weld Stud Fixing
	Identification Plate Position	none
	Releasable Closure	Yes
	Tie Closure	ladder style
	Variant	No Serration
	Width W (Imperial)	0.4"
	Width W (Metric)	10.0mm
	Height H (Imperial)	0.06"
	Height H (Metric)	1.4mm
	Height H2 (Imperial)	0.81"
	Height H2 (Metric)	20.5mm
	Bundle Diameter Min. (Imperial)	0.24"
	Bundle Diameter Min. (Metric)	6.0mm

150-28140

HellermannTyton

Product Dimensions	Bundle Diameter Max. (Imperial)	1.5"
	Bundle Diameter Max. (Metric)	38.0mm
	Stud Diameter (Imperial)	0.2"
	Stud Diameter (Metric)	5.0 mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500
	Package Quantity (Metric)	500Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces
	Weight (Metric)	1.86kg