

150-45397

HellermannTyton



Article Number: 150-45397

Description: Standoff Bundling Clip, Panel Thickness .02"—.07", 1.6" Long, PA66HIRHS, Black, 500/box

Base Data		
	Local Order Number	150-45397
	Type	STAND OFF CLIP
	Color	Black (BK)
	Features and benefits	• Standoff design secures the bundle away from the mounting hole. • Design provides low insertion force and high extraction force.
	Quantity Per	bag
	Product Description	Bundling Clips are designed to provide simple and easy methods of securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using bundle or cable ties. The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standard bundling clips are available as well as standoff and stud mount versions.
	Short Description	Standoff Bundling Clip, Panel Thickness .02"—.07", 1.6" Long, PA66HIRHS, Black, 500/box
Product Dimensions		
	Length L (Imperial)	1.6"
	Length L (Metric)	40.0mm
	Length L2 (Imperial)	1.2"
	Fixation Method	Arrowhead
	Length L2 (Metric)	31.0mm
	Height H (Imperial)	0.6"
	Disc Diameter (Imperial)	0.71"
	Disc Diameter (Metric)	18.0mm
	Panel Thickness Max. (Imperial)	0.02"
	Panel Thickness Max. (Metric)	1.6mm
	Panel Thickness Min. (Imperial)	0.02"
	Panel Thickness Min. (Metric)	0.4mm
	Mounting Hole Diameter D (Imperial)	0.26 - 0.27"
	Mounting Hole Diameter D (Metric)	6.5 - 6.8 mm

150-45397

HellermannTyton

Product Dimensions	Mounting Hole Diameter D Min. (Imperial)	0.283"
	Mounting Hole Diameter D Max. (Imperial)	0.26"
Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)
	Material Shortcut	PA66HIRHS
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500
	Package Quantity (Metric)	500Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces
	Weight (Metric)	1.825kg