

150-95500

HellermannTyton

Article Number: 150-95500



Description: Bundling Clip w Fir Tree, 1.46"L, .03"-.06" Panel Thick, .26"-.28" Hole Dia, PA66HIRHS, Bk, 1000/pkg

Base Data		
	Local Order Number	150-95500
	Type	TC5FT6S
	Color	Black (BK)
	Features and benefits	Standard tape clips secure the bundle directly above the mounting hole.
	Quantity Per	bag
	Short Description	Bundling Clip w Fir Tree, 1.46"L, .03"-.06" Panel Thick, .26"-.28" Hole Dia, PA66HIRHS, Bk, 1000/pkg
Product Dimensions		
	Length L (Imperial)	1.46"
	Length L (Metric)	37.0mm
	Fixation Method	Fir Tree
	Width W (Imperial)	0.32"
	Width W (Metric)	8.0mm
	Height H (Imperial)	0.32"
	Height H (Metric)	8.2mm
	Height H2 (Imperial)	0.2"
	Height H2 (Metric)	5.0mm
	Panel Thickness Max. (Imperial)	0.06"
	Panel Thickness Max. (Metric)	1.5mm
	Panel Thickness Min. (Imperial)	0.03"
	Panel Thickness Min. (Metric)	0.75mm
	Mounting Hole Diameter D (Metric)	6.4 - 7.1 mm
	Mounting Hole Diameter D Min. (Imperial)	0.26"
	Mounting Hole Diameter D Max. (Imperial)	0.28"

150-95500



Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)
	Material Shortcut	PA66HIRHS
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1000
	Package Quantity (Metric)	1000Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces
	Weight (Metric)	0.55kg