

151-00016

HellermannTyton

Article Number: 151-00016

 Description: Standoff Stud Mnt Tape Clip Long 2.17" Weld Stud Mnt .2"
PA66HIRHS Black 500/pkg


Base Data		
	Local Order Number	151-00016
	Type	BC30
	Color	Black (BK)
	Features and benefits	Tape clips are designed to provide simple and easy methods of securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties. The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standoff stud mount tape clips are easily inserted on a 5mm stud and secure the bundle away from the mounting hole.
	Quantity Per	bag
	Short Description	Standoff Stud Mnt Tape Clip Long 2.17" Weld Stud Mnt .2" PA66HIRHS Black 500/pkg
Product Dimensions		
	Length L (Imperial)	2.2"
	Length L (Metric)	55.0mm
	Fixation Method	Weld Stud Fixing
	Length L2 (Metric)	30.0mm
	Width W (Imperial)	1.2"
	Width W (Metric)	30.0mm
	Height H (Imperial)	0.47"
	Height H (Metric)	12mm
	Diameter D (imperial)	0.2"
	Diameter D (metric)	5mm
	Stud Diameter (Imperial)	0.2"
	Stud Diameter (Metric)	5.0 mm

151-00016



Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)
	Material Shortcut	PA66HIRHS
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1000
	Package Quantity (Metric)	1000Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces
	Weight (Metric)	0.96kg