

151-00077

# HellermannTyton



Article Number: 151-00077

Description: Bundling Clip, 2.0" Long, .03"—.06" Panel Thickness, Hole Diameter 0.26", PA66HS, Black, 100/pkg

Base Data		
	Local Order Number	151-00077
	Type	CH20D6
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Clip can be installed by hand without the need for a tool</li> <li>• Design provides low insertion force and high extraction force ideal for the production environment.</li> <li>• Clip secures bundle away from areas that can cause rubbing and chafing.</li> </ul>
	Quantity Per	bag
	Product Description	Bundling clips are designed to provide simple and easy methods of securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties. The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standard bundling clips are available as well as standoff and stud mount versions.
	Short Description	Bundling Clip, 2.0" Long, .03"—.06" Panel Thickness, Hole Diameter 0.26", PA66HS, Black, 100/pkg
Product Dimensions		
	Length L (Imperial)	2.0"
	Length L (Metric)	50.0mm
	Length L2 (Imperial)	0.8"
	Fixation Method	Arrowhead
	Length L2 (Metric)	20.0mm
	Height H (Imperial)	0.3"
	Panel Thickness Max. (Imperial)	0.06"
	Panel Thickness Max. (Metric)	1.40mm
	Panel Thickness Min. (Imperial)	0.03"
	Panel Thickness Min. (Metric)	0.60mm
	Mounting Hole Diameter D (Imperial)	0.25"
	Mounting Hole Diameter D (Metric)	6.4 - 7.0 mm

151-00077



Material and Specifications		
	Material	Polyamide 6.6 heat stabilized (PA66HS)
	Material Shortcut	PA66HS
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces
	Weight (Metric)	2.141kg