

151-00096

Article Number: 151-00096

Description: Pipe and Hose Clips, Max Bundle Diameter .49", Height .72", Width .39", PA66, Black, 100/pkg



Base Data	
Local Order Number	151-00096
Type	IPC10AH
Color	Black (BK)
Features and benefits	<ul style="list-style-type: none"> <li>• Clips offer a easy securing option when cable ties can't be used.</li> <li>• Clips can be attached to the panel prior to installing the pipe or hose.</li> </ul>
Quantity Per	bag
Product Description	Pipe and hose clips offer simple and secure installation of pipes or hoses to panels. Simply push the pipe into the clip for a firm and secure fixing. These parts can also be connected together offering a greater choice of installation options.
Short Description	Pipe and Hose Clips, Max Bundle Diameter .49", Height .72", Width .39", PA66, Black, 100/pkg
Product Dimensions	
Length L (Imperial)	0.87"
Length L (Metric)	22.2mm
Width W (Imperial)	0.39"
Width W (Metric)	10.0mm
Height H (Imperial)	0.72"
Height H (Metric)	18.4mm
Bundle Diameter Min. (Imperial)	0.33"
Bundle Diameter Min. (Metric)	8.5mm
Bundle Diameter Max. (Imperial)	0.49"
Bundle Diameter Max. (Metric)	12.5mm
Disc Diameter (Imperial)	0.87"
Disc Diameter (Metric)	22.0mm
Panel Thickness Max. (Imperial)	0.06"
Panel Thickness Max. (Metric)	1.6mm
Panel Thickness Min. (Imperial)	0.02"

151-00096



Product Dimensions	Panel Thickness Min. (Metric)	0.6mm
	Mounting Hole Diameter D (Imperial)	0.25"
	Mounting Hole Diameter D (Metric)	6.3 mm
	Mounting Hole Diameter D Max. (Imperial)	0.255"
	Stud Diameter (Imperial)	0.2"
Material and Specifications		
	Material	Polyamide 6.6, high impact modified (PA66HIR)
	Material Shortcut	PA66HIR
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +176°F (-40°C to +80°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces