

151-00180

HellermannTyton



Article Number: 151-00180

Description: Connector Clip; Hole Dia. 6.2X12.2mm; Panel 0.6-6.0mm/ PA66HIRHS; Black; 1000/Pack

| | | |
|--------------------|--|--|
| Base Data | | |
| | Local Order Number | 151-00180 |
| | Type | YCCFT62x122 |
| | Color | Black (BK) |
| | Features and benefits | <ul style="list-style-type: none"> • HellermannTyton connector clips provide a simple and easy method for mounting connectors to a mounting surface in a variety of applications. • Detailed designs include anti-rattle disc features, anti-rotation oval fir trees, and clamps for mounting on edges. • HellermannTyton offers an assortment of connector clips that are available for a variety of connector slot designs found on most of the largest global connector manufacturers. |
| | Quantity Per | pieces |
| | Product Description | HellermannTyton connector clips, for oval holes, are mounted simply by pushing them onto the corresponding clip. The clips provide a wide range of mounting options with anti-rattle and anti-rotation features. The fir tree locks into place when inserted into the hole palpably and ensures a secure fixing at all times. |
| | Short Description | Connector Clip; Hole Dia. 6.2X12.2mm; Panel 0.6-6.0mm/ PA66HIRHS; Black; 1000/Pack |
| Product Dimensions | | |
| | Length L (Imperial) | 0.83" |
| | Fixation Method | Fir Tree for oval holes |
| | Width W (Imperial) | 0.63" |
| | Width W (Metric) | 16.0mm |
| | Height H (Imperial) | 0.71" |
| | Height H (Metric) | 18.0mm |
| | Panel Thickness Max. (Imperial) | 0.24" |
| | Panel Thickness Max. (Metric) | 6.0mm |
| | Panel Thickness Min. (Imperial) | 0.02" |
| | Panel Thickness Min. (Metric) | 0.6mm |
| | Mounting Hole Diameter D (Metric) | 6.2 x 12.2 mm |
| | Mounting Hole Diameter D Min. (Imperial) | 0.244" |

151-00180

HellermannTyton

| | | |
|-----------------------------|--|---|
| Product Dimensions | Mounting Hole Diameter D Max. (Imperial) | 0.48" |
| Material and Specifications | | |
| | Material | Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS) |
| | Material Shortcut | PA66HIRHS |
| | Flammability | UL 94 HB |
| | Operating Temperature | -40°F to +221°F (-40°C to +105°C) |
| | REACH Compliant (Article 33) | Yes |
| | ROHS Compliant | Yes |
| Logistic and Packaging | | |
| | Package Quantity (Imperial) | 1000 |
| | Package Quantity (Metric) | 1000Pieces |
| | Customs Number(Schedule B) | 3926909987 |
| | Content Unit (BMEcat) | pieces |
| | Weight (Metric) | 1.18kg |