

151-00232

HellermannTyton



Article Number: 151-00232

Description: Push-Button Mount, .25" Hole Dia, .12" Max Panel, .2" Max Tie Width, PA66, Natural, 100/pkg

Base Data		
	Local Order Number	PBM9C2
	Type	PBM
	Color	Natural (NA)
	Features and benefits	<ul style="list-style-type: none"> • Push Mounts, when used with standard cable ties, provide a permanent bundling solution below a panel. • The "button" style head is ideal for space constrained areas and is easily inserted through a pre-drilled hole.
	Quantity Per	bag
	Product Description	HellermannTyton push mounts are used with our standard cable ties and offer a permanent bundling solution for installation below or underneath a panel. Designed for simple installation by pushing the mount through a pre-drilled hole. The low profile "button" style head is suitable in space constrained areas.
	Short Description	Push-Button Mount, .25" Hole Dia, .12" Max Panel, .2" Max Tie Width, PA66, Natural, 100/pkg
Product Dimensions		
	Width W (Imperial)	0.26"
	Width W (Metric)	6.6mm
	Cable Tie Width Max. (Imperial)	0.2"
	Cable Tie Width Max. (Metric)	5.0mm
	Height H (Imperial)	.40"
	Height H (Metric)	10.20mm
	Height H2 (Imperial)	.08"
	Height H2 (Metric)	2.0mm
	Panel Thickness Max. (Imperial)	0.12"
	Panel Thickness Max. (Metric)	3.0mm
	Mounting Hole Diameter D (Imperial)	0.25"
	Mounting Hole Diameter D (Metric)	6.25 - 6.55 mm
	Mounting Hole Diameter D Max. (Imperial)	0.29"

151-00232



Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	ROHS Compliant	Yes
	Certification/Specification	UL
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100
	Customs Number(Schedule B)	3926909987