

151-00291

HellermannTyton

Article Number: 151-00291

Description: Cable Tie Anchor Mount, .20 x.70" Hole Dia, .20" Max Tie Width, PA66, Black, 100/pkg



Base Data		
	Local Order Number	CTAP20C2
	Type	CTAP2
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Mount provides a "stand-off" for perpendicular bundles. • Secures with a single screw with the option of an additional screw, providing extra stability.
	Quantity Per	bag
	Product Description	HellermannTyton cable tie anchor plates are designed as a "stand-off" mount for perpendicular wire bundles. These mounts offer an elongated mounting hole for easier alignment of wire bundles. The mounts are installed quick and easy by securing a single screw, with the option of an additional screw for maximum stability.
	Short Description	Cable Tie Anchor Mount, .20 x.70" Hole Dia, .20" Max Tie Width, PA66, Black, 100/pkg
Product Dimensions		
	Length L (Imperial)	2.13"
	Length L (Metric)	54.1mm
	Fixation Method	Screw Mounting and Rivet
	Width W (Imperial)	0.5"
	Width W (Metric)	12.7mm
	Cable Tie Width Max. (Imperial)	0.2"
	Cable Tie Width Max. (Metric)	5.0mm
	Height H (Imperial)	.14"
	Height H (Metric)	3.50mm
	Mounting Hole Diameter D (Imperial)	0.2 x 0.7"
	Mounting Hole Diameter D (Metric)	5.0 x 19.0 mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)

151-00291



Material and Specifications	Material Shortcut	PA66
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	ROHS Compliant	Yes
	Certification/Specification	UL
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100