

151-00319

HellermannTyton



Article Number: 151-00319

Description: Screw-Mount Base, 1.12" x 1.12", .18" Max Tie Width, .18" Hole Dia, PA66, White, 500/pkg

Base Data		
	Local Order Number	MB410H4
	Type	MB4
	Color	White (WH)
	Features and benefits	<ul style="list-style-type: none"> • For use with 18 through 50 pound cable ties to provide stability when securing bundles. • Secures with two or four screws; providing multiple options. • 4 way opening allows cable ties to be installed parallel or perpendicular to wire bundles.
	Quantity Per	bag
	Product Description	HellermannTyton screw fastened mounting bases are used with 18 through 150 pound cable ties to provide stability when securing bundles. The mounts are installed by securing two or four screws. The 4 way opening allows the cable ties to be inserted parallel or perpendicular to the wire bundles.
	Short Description	Screw-Mount Base, 1.12" x 1.12", .18" Max Tie Width, .18" Hole Dia, PA66, White, 500/pkg
Product Dimensions		
	Length L (Imperial)	1.12"
	Length L (Metric)	28.5mm
	Fixation Method	Screw Mounting and Rivet
	Width W (Imperial)	1.12"
	Width W (Metric)	28.5mm
	Cable Tie Width Max. (Imperial)	0.18"
	Cable Tie Width Max. (Metric)	4.6mm
	Height H (Imperial)	.19"
	Height H (Metric)	4.80mm
	Mounting Hole Diameter D (Imperial)	0.18"
	Mounting Hole Diameter D (Metric)	4.6 mm
	Mounting Hole Centers (Imperial)	0.8"

151-00319



Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	ROHS Compliant	Yes
	Certification/Specification	UL
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500
	Package Quantity (Metric)	500
	Customs Number(Schedule B)	3926909987