

151-00358

HellermannTyton



Article Number: 151-00358

Description: Lashing Tie Mount, .73" x 1.5", .25" Screw, PA66HS, Black, 100/pkg

Base Data		
	Local Order Number	LTM2500C2
	Type	LTM250
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> The strap is parallel to the mount when inserted into the head, providing a mounting point for where the cable ties.
	Quantity Per	bag
	Product Description	The Lashing Tie Mount is designed to snap into the T250 lashing tie. The tie head is assembled perpendicular to the mount. The lashing tie mount is recommended for indoor or outdoor wall mount cable applications.
	Short Description	Lashing Tie Mount, .73" x 1.5", .25" Screw, PA66HS, Black, 100/pkg
Product Dimensions		
	Length L (Imperial)	1.5"
	Length L (Metric)	37.1mm
	Fixation Method	Screw Mounting and Rivet
	Width W (Imperial)	0.73"
	Width W (Metric)	18.5mm
	Cable Tie Width Max. (Imperial)	0.49"
	Cable Tie Width Max. (Metric)	12.5mm
	Height H (Imperial)	.38"
	Height H (Metric)	9.60mm
	Mounting Hole Diameter D (Imperial)	0.26"
	Mounting Hole Diameter D (Metric)	6.6 mm
Material and Specifications		
	Material	Polyamide 6.6 heat stabilized (PA66HS)
	Material Shortcut	PA66HS

151-00358



Material and Specifications	Flammability	UL 94 V2
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces