

151-00436

HellermannTyton



Article Number: 151-00436

Description: Heavy-Duty Mount, .1875" Mounting Hole, 115lb-ft Max Torque, PA66HIRHSUV, Black, 500/pkg

Base Data		
	Local Order Number	HDM190HIRH4
	Type	HDM19
	Color	Black (BK)
	Features and benefits	• Mount and tie combination makes it easy to service bundles in the field. • Made from impact modified, heat stabilized, UV resistant material, ideal for heavy duty environments. • Eliminates the needs for multiple sized fix diameter clamps.
	Quantity Per	bag
	Product Description	HellermannTyton mounts when used with a cable tie eliminates the need to carry multiple sizes of fixed bundle diameter clamps, which reduces inventory and purchasing costs while simplifying the assembly process.
	Short Description	Heavy-Duty Mount, .1875" Mounting Hole, 115lb-ft Max Torque, PA66HIRHSUV, Black, 500/pkg
Product Dimensions		
	Length L (Imperial)	1.4"
	Length L (Metric)	36.3mm
	Fixation Method	Screw Mounting and Rivet
	Width W (Imperial)	0.8"
	Width W (Metric)	19.3mm
	Cable Tie Width Max. (Imperial)	0.5"
	Cable Tie Width Max. (Metric)	12.7mm
	Width W2 (Imperial)	0.5"
	Width W2 (Metric)	13.3mm
	Height H (Imperial)	.70"
	Height H (Metric)	16.70mm
	Height H2 (Imperial)	.30"
	Height H2 (Metric)	8.0mm
	Mounting Hole Diameter D (Imperial)	0.2"

151-00436



Product Dimensions	Mounting Hole Diameter D (Metric)	4.7 mm
Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
	Material Shortcut	PA66HIRHSUV
	Flammability	UL 94 HB
	Maximum Torque (kgf-cm)	132.5kgf-cm
	Maximum Torque (lbf-ft)	9.583lbf-ft
	Operating Temperature	-40°F to +230°F (-40°C to +110°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500
	Package Quantity (Metric)	500
	Customs Number(Schedule B)	3926909987