

151-00446

HellermannTyton



Article Number: 151-00446

Description: High-Torque Mount, .5" Mounting Hole, 114lb-ft Max Torque, PA66HIRHSUV, Black, 100/pkg

Base Data		
	Local Order Number	HDM500BHIHSUVC2
	Type	HDM500
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Mount and tie combination makes it easy to service bundles in the field. • Made from impact modified, heat stabilized, UV resistant material, ideal for heavy duty environments. • Eliminates the needs for multiple sized fix diameter clamps.
	Quantity Per	bag
	Product Description	This heavy duty mount, when used with a cable tie eliminates the need to carry multiple sizes of fixed bundle diameter clamps; which reduces inventory and purchasing costs while simplifying the assembly process.
	Short Description	High-Torque Mount, .5" Mounting Hole, 114lb-ft Max Torque, PA66HIRHSUV, Black, 100/pkg
Product Dimensions		
	Length L (Imperial)	1.9"
	Length L (Metric)	47.0mm
	Fixation Method	Screw Mounting and Rivet
	Width W (Imperial)	1.0"
	Width W (Metric)	25.0mm
	Cable Tie Width Max. (Imperial)	0.5"
	Cable Tie Width Max. (Metric)	12.7mm
	Height H (Imperial)	.80"
	Height H (Metric)	20.70mm
	Mounting Hole Diameter D (Imperial)	0.5"
	Mounting Hole Diameter D (Metric)	12.7 mm
Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)

151-00446



Material and Specifications	Material Shortcut	PA66HIRHS
	Flammability	UL 94 HB
	Maximum Torque (lbf-ft)	114lbf-ft
	Maximum Torque (kgf-cm)	1576kgf-cm
	Operating Temperature	-40°F to +230°F (-40°C to +110°C)
	REACH Compliant (Article 33)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces
	Weight (Metric)	15.56kg