

151-00758

HellermannTyton



Article Number: 151-00758

Description: Cable Tie Anchor Mount, .20" Hole Dia, .20" Max Tie Width, PEEK, Beige, 100/pkg

Base Data		
	Local Order Number	151-00758
	Type	CTAM2
	Color	Beige (BGE)
	Features and benefits	• PEEK mounts provide excellent resistance to extreme temperature environments. • 4-way entry allowing the cable tie to secure bundles running parallel or perpendicular.
	Quantity Per	bag
	Product Description	HellermannTyton cable tie anchor mounts are designed with a 4-way entry allowing the cable tie to secure bundles running parallel or perpendicular. The mounts are installed quick and easy by securing a single screw.
	Short Description	Cable Tie Anchor Mount, .20" Hole Dia, .20" Max Tie Width, PEEK, Beige, 100/pkg
Product Dimensions		
	Length L (Imperial)	0.81"
	Length L (Metric)	20.5mm
	Recommended Cable Ties	T18 - T50
	Fixation Method	Screw Mounting and Rivet
	Width W (Imperial)	0.4"
	Width W (Metric)	10.2mm
	Cable Tie Width Max. (Imperial)	0.2"
	Cable Tie Width Max. (Metric)	5.0mm
	Height H (Imperial)	0.22"
	Height H (Metric)	5.5mm
	Height H2 (Imperial)	0.075"
	Height H2 (Metric)	1.9mm
	Mounting Hole Diameter D (Imperial)	0.2"
	Mounting Hole Diameter D (Metric)	5.2 mm

151-00758



Material and Specifications		
	Material	Polyetheretherketone (PEEK)
	Material Shortcut	PEEK
	Flammability	UL 94 V0
	Operating Temperature	-67°F to +464°F (-55°C to +240°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100Pieces
	Content Unit (BMEcat)	pieces
	Weight (Metric)	2kg