

151-00973

HellermannTyton



Article Number: 151-00973

Description: H-Mount for .38" standard bolts and Huck-Spin bolts,
PA66HIRHSUV, Black, 900/pkg

Base Data		
	Local Order Number	151-00973
	Type	HM4
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • H-Mounts utilize existing frame rail bolts eliminating the need for additional fasteners. • When used with cable ties, the H-Mounts eliminate the need to carry multiple sizes of fixed bundle diameter clamps which reduces inventory and purchasing costs. • Ability to position bundles in up to three locations, provides multiple use options.
	Quantity Per	bag
	Product Description	H-mounts offer a secure bundling solution that utilizes existing frame rail bolts which reduces component costs and improves installation time. The H-mounts have three bundle mounting locations each accommodating ties up to 1/2" wide. The top tie slot allows the bundle to be positioned directly over the bolt. The two curved tie slots on the sides position the bundles adjacent to the bolt yet away from the frame.
	Short Description	H-Mount for .38" standard bolts and Huck-Spin bolts, PA66HIRHSUV, Black, 900/pkg
Product Dimensions		
	Length L (Imperial)	2.0"
	Length L (Metric)	50.0mm
	Fixation Method	thread-bolt
	Width W (Imperial)	1.0"
	Width W (Metric)	26.0mm
	Cable Tie Width Max. (Imperial)	0.052"
	Cable Tie Width Max. (Metric)	13.2mm
	Height H (Imperial)	1.10"
	Height H (Metric)	28.0mm
	Stud Diameter (Imperial)	0.625"
	Stud Diameter (Metric)	15.9 mm

151-00973



Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
	Material Shortcut	PA66HIRHSUV
	Flammability	UL 94 HB
	Operating Temperature	-65°F to +212°F (-54°C to +100°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	900
	Package Quantity (Metric)	900
	Customs Number(Schedule B)	3926909987