

151-01633

# HellermannTyton

Article Number: 151-01633



Description: VHB Adhesive Base, 1.49" x 1.49", .35" Max Tie Width, .19" Hole Dia, PA66HIRHSUV/Acrylic, Black, 100/pkg

Base Data		
	Local Order Number	151-01633
	Type	MB5A
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• For use with 18 through 150 pound HellermannTyton cable ties.</li> <li>• Extremely durable adhesive achieves high pull-off force and is unaffected by vibration.</li> <li>• Multiple sizes accommodate a range of cable ties.</li> <li>• 4-way opening allows cable ties to be installed parallel or perpendicular to wire bundles.</li> <li>• Predrilled holes extend mounting options and security.</li> <li>• Mount made of proprietary, impact-modified PA66 material for extraordinary durability, and is heat stabilized and UV resistant for extended life outdoors.</li> <li>• Peel and stick for quick, convenient use in extreme-duty applications.</li> </ul>
	Quantity Per	bag
	Product Description	HellermannTyton offers adhesive mounts in a variety of sizes to match your cable tie size and extreme-duty application needs. The mount features 3M™ VHB™ (Very High Bond) adhesive, which actually builds strength over time and holds securely to difficult materials such as aluminum, steel, plastics and painted and powder-coated surfaces.
	Short Description	VHB Adhesive Base, 1.49" x 1.49", .35" Max Tie Width, .19" Hole Dia, PA66HIRHSUV/Acrylic, Black, 100/pkg
Product Dimensions		
	Length L (Imperial)	1.49"
	Length L (Metric)	37.7mm
	Fixation Method	Adhesive
	Width W (Imperial)	1.49"
	Width W (Metric)	37.7mm
	Cable Tie Width Max. (Imperial)	0.35"
	Cable Tie Width Max. (Metric)	8.9mm
	Height H (Imperial)	.28"
	Height H (Metric)	7.10mm
	Mounting Hole Diameter D (Imperial)	0.19"

151-01633



Product Dimensions	Mounting Hole Diameter D (Metric)	4.8 mm
	Mounting Hole Diameter D Min. (Imperial)	0.19"
	Mounting Hole Diameter D Max. (Imperial)	0.19"
	Mounting Hole Centers (Imperial)	1"
Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
	Material Shortcut	PA66HIRHSUV
	Adhesive	Acrylic foam
	Flammability	UL 94 V2 (excluding adhesive)
	Operating Temperature	-40°F to +176°F (-40°C to +80°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100
	Customs Number(Schedule B)	3926909987