

151-07500

HellermannTyton



Article Number: 151-07500

Description: Heavy-Duty Mount, .5" Mounting Hole, 40lb-ft Max Torque, PA66HIRHSUV, Black, 500/pkg

Base Data		
	Local Order Number	HDM501HIHSUVH4
	Type	HDM501
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Mount and tie combination makes it easy to service bundles in the field. • Made from impact modified, heat stabilized, UV resistant material, ideal for heavy duty environments. • Eliminates the needs for multiple sized fix diameter clamps.
	Quantity Per	bag
	Product Description	This mount, when used with a cable tie eliminates the need to carry multiple sizes of fixed bundle diameter clamps; which reduces inventory and purchasing costs while simplifying the assembly process.
	Short Description	Heavy-Duty Mount, .5" Mounting Hole, 40lb-ft Max Torque, PA66HIRHSUV, Black, 500/pkg
Product Dimensions		
	Length L (Imperial)	1.8"
	Length L (Metric)	46.0mm
	Fixation Method	Screw Mounting and Rivet
	Width W (Imperial)	1.0"
	Width W (Metric)	24.0mm
	Cable Tie Width Max. (Imperial)	0.5"
	Cable Tie Width Max. (Metric)	12.7mm
	Height H (Imperial)	.80"
	Height H (Metric)	20.70mm
	Mounting Hole Diameter D (Imperial)	0.5"
	Mounting Hole Diameter D (Metric)	12.7 mm
Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)

151-07500



Material and Specifications	Material Shortcut	PA66HIRHS
	Flammability	UL 94 V2
	Maximum Torque (kgf-cm)	553kgf-cm
	Maximum Torque (lbf-ft)	40lbf-ft
	Operating Temperature	-40°F to +230°F (-40°C to +110°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500
	Package Quantity (Metric)	500Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces
	Weight (Metric)	1kg