

151-10905

HellermannTyton



Article Number: 151-10905

Description: Q Mount with Adhesive, 1.2" x 1.2" x 0.21", 4 way entry for Q18 thru Q50 ties, PA66, White, 100/bag

Base Data		
	Local Order Number	151-10905
	Type	QM30A
	Color	Natural (NA)
	Features and benefits	• 2- or 4-way entry options for the Q Tie, offering flexibility and stability
	Quantity Per	bag
	Product Description	Q Mounts are designed to work exclusively with the Q Tie cable tie series. This mounting component is available with adhesive or can be secured with screws. The Q Mount allows either a 2- or 4-way entry for the Q Tie, providing a quick and simple insertion into the mount. Once in place, the Q Tie will not slip out, even in vertical mounting applications.
	Short Description	Q Mount with Adhesive, 1.2" x 1.2" x 0.21", 4 way entry for Q18 thru Q50 ties, PA66, White, 100/bag
Product Dimensions		
	Length L (Imperial)	1.2"
	Length L (Metric)	30.0mm
	Fixation Method	Screw Mounting and Adhesive
	Width W (Imperial)	1.2"
	Width W (Metric)	30.0mm
	Cable Tie Width Max. (Imperial)	0.2"
	Cable Tie Width Max. (Metric)	5.1mm
	Height H (Imperial)	0.21"
	Height H (Metric)	4.5mm
	Mounting Hole Diameter D (Imperial)	0.16"
	Mounting Hole Diameter D (Metric)	4.1 mm
	Mounting Hole Diameter D Min. (Imperial)	0.16"
	Mounting Hole Centers (Imperial)	0.83"

151-10905



Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Adhesive	Synthetic rubber with base of polyethylene foam
	Adhesive Operating Temperature	-40°F to +140°F (-40°C to +60°C)
	Flammability	UL 94 V2 (excluding adhesive)
	Halogenfree	Yes
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces