

151-10911



Article Number: 151-10911

Description: Q Mount, 0.12" Hole Dia, 0.79" x 0.79" x 0.17", 4 way entry for Q18–Q30 ties, PA66, Black, 100/bag

Base Data		
	Local Order Number	151-10911
	Type	QM20
	Color	Black (BK)
	Features and benefits	• 2- or 4-way entry options for the Q Tie, offering flexibility and stability
	Quantity Per	bag
	Product Description	Q Mounts are designed to work exclusively with the Q Tie cable tie series. This mounting component is available with adhesive or can be secured with screws. The Q Mount allows either a 2- or 4-way entry for the Q Tie, providing a quick and simple insertion into the mount. Once in place, the Q Tie will not slip out, even in vertical mounting applications.
	Short Description	Q Mount, 0.12" Hole Dia, 0.79" x 0.79" x 0.17", 4 way entry for Q18–Q30 ties, PA66, Black, 100/bag
Product Dimensions		
	Length L (Imperial)	0.79"
	Length L (Metric)	20.0mm
	Fixation Method	Screw Mounting and Rivet
	Width W (Imperial)	0.79"
	Width W (Metric)	20.0mm
	Cable Tie Width Max. (Imperial)	0.14"
	Cable Tie Width Max. (Metric)	4.0mm
	Height H (Imperial)	0.14"
	Height H (Metric)	3.7mm
	Mounting Hole Diameter D (Imperial)	0.12"
	Mounting Hole Diameter D (Metric)	3.1 mm
	Mounting Hole Diameter D Min. (Imperial)	0.12"
	Mounting Hole Centers (Imperial)	0.53"

151-10911



Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
	Certification/Specification	UL ANSI/UL 62275
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100Pieces
	Content Unit (BMEcat)	pieces