

151-10930

HellermannTyton



Article Number: 151-10930

Description: Q Mount, M4 Screw, 0.83" x 0.38" x 0.26", For Q18–Q50 ties, PA66, Black, 100/bag

Base Data		
	Local Order Number	151-10930
	Type	CTQM5
	Color	Black (BK)
	Features and benefits	• 2- or 4-way entry options for the Q Tie, offering flexibility and stability
	Quantity Per	bag
	Product Description	Q Mounts are designed to work exclusively with the Q Tie cable tie series. This mounting component is available with adhesive or can be secured with screws. The Q Mount allows either a 2- or 4-way entry for the Q Tie, providing a quick and simple insertion into the mount. Once in place, the Q Tie will not slip out, even in vertical mounting applications.
	Short Description	Q Mount, M4 Screw, 0.83" x 0.38" x 0.26", For Q18–Q50 ties, PA66, Black, 100/bag
Product Dimensions		
	Length L (Imperial)	0.83"
	Length L (Metric)	21.0mm
	Fixation Method	Screw Mounting and Rivet
	Width W (Imperial)	0.38"
	Width W (Metric)	9.5mm
	Cable Tie Width Max. (Imperial)	0.2"
	Cable Tie Width Max. (Metric)	5.0mm
	Height H (Imperial)	0.26"
	Height H (Metric)	6.7mm
	Mounting Hole Diameter D (Imperial)	0.175"
	Mounting Hole Diameter D (Metric)	4.5 mm
	Mounting Hole Diameter D Min. (Imperial)	0.18"

151-10930



Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
	Certification/Specification	UL ANSI/UL 1565
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces