

151-10952

HellermannTyton



Article Number: 151-10952

Description: Q Tag, Right Angled, 3.9" x 1.7", For Q18 thru Q30 ties, PA66, White, 50/bag

Base Data		
	Local Order Number	151-10952
	Type	QT7040S
	Color	White (WH)
	Features and benefits	• Opening on the tag allows the Q Tie to be easily inserted, providing a secure identification solution
	Quantity Per	bag
	Product Description	Q Tags are used in conjunction with the Q Tie cable tie series for labeling cables and wire bundles. The Q Tie is simply inserted through the Q Tag opening, providing a quick identification solution that also securely fastens the cable or wire bundle. The Q Tag can be marked using a Sharpie felt tip pen, or by applying a thermal transfer label that has been pre-printed using the TagPrint Pro 3.0 label creation software and a HellermannTyton thermal transfer printer.
	Short Description	Q Tag, Right Angled, 3.9" x 1.7", For Q18 thru Q30 ties, PA66, White, 50/bag
Product Dimensions		
	Length L (Imperial)	3.46"
	Length L (Metric)	88.0mm
	Length L2 (Imperial)	2.76"
	Length L2 (Metric)	70.0mm
	Variant	Other
	Width W (Imperial)	1.65"
	Width W (Metric)	42.0mm
	Cable Tie Width Max. (Imperial)	0.14"
	Cable Tie Width Max. (Metric)	3.6mm
	Thickness T (Imperial)	0.055"
	Thickness T (Metric)	1.4mm
	Width of printable area (metric)	40.00mm
	Width of Printable Area (imperial)	1.57"

151-10952



Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	50
	Package Quantity (Metric)	50Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces