

151-14303

HellermannTyton



Article Number: 151-14303

Description: Fir Tree Mount Tube Clip Mounting Hole Dia .25" Panel Thickness .12" PA66HIRHS, Black 100/pkg

Base Data		
	Local Order Number	PC15FT7
	Type	PC15FT7
	Color	Black (BK)
	Features and benefits	The clips CTC and PC are designed for fixation and bundling of convoluted tubes and pipes. Due to several designs and fixing parts, the clips can be use for nearly every application.
	Quantity Per	bag
Product Dimensions	Short Description	Fir Tree Mount Tube Clip Mounting Hole Dia .25" Panel Thickness .12" PA66HIRHS, Black 100/pkg
	Length L (Imperial)	0.62"
	Length L (Metric)	15.7mm
	Fixation Method	Fir Tree
	Width W (Imperial)	0.85"
	Width W (Metric)	21.6mm
	Height H (Imperial)	1.5"
	Height H (Metric)	38.1mm
	Height H2 (Imperial)	1.07"
	Height H2 (Metric)	26.7mm
	Bundle Diameter Max. (Imperial)	0.62"
	Bundle Diameter Max. (Metric)	15.7mm
	Disc Diameter (Imperial)	0.9"
	Disc Diameter (Metric)	21.6mm
	Panel Thickness Max. (Imperial)	0.31"
	Panel Thickness Max. (Metric)	6.0mm
	Panel Thickness Min. (Imperial)	0.04"

151-14303

HellermannTyton

Product Dimensions	Panel Thickness Min. (Metric)	1.0mm
	Mounting Hole Diameter D (Metric)	6.4 - 6.8 mm
	Mounting Hole Diameter D Min. (Imperial)	0.26"
	Mounting Hole Diameter D Max. (Imperial)	0.26"
Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)
	Material Shortcut	PA66HIRHS
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1000
	Package Quantity (Metric)	1000
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces