

151-24219

# HellermannTyton

Article Number: 151-24219

Description: Cable Tie Mounting Plates, .50" x 3.00", T18-T50 Cable Ties, #6 (M3) Screw, PA66, Natural, 100/pk



Base Data		
	Local Order Number	MP2M3.NN3P
	Type	MP2M3
	Color	Natural (NA)
	Features and benefits	<ul style="list-style-type: none"> <li>• Mounting plates allow multiple bundles to run parallel.</li> <li>• The mounts are secured using two screws, while the bundles are attached using cable ties in any of the available slots.</li> </ul>
	Quantity Per	bag
	Product Description	Mounting Plates allow multiple cables to be run in parallel. Mounts are secured with two screws. Cables are attached to the plates by running a cable tie through any of the available slots.
	Short Description	Cable Tie Mounting Plates, .50" x 3.00", T18-T50 Cable Ties, #6 (M3) Screw, PA66, Natural, 100/pk
Product Dimensions		
	Length L (Imperial)	3.0"
	Length L (Metric)	76.2mm
	Fixation Method	Screw Mounting and Rivet
	Number of Bundles	2
	Width W (Imperial)	0.5"
	Width W (Metric)	12.7mm
	Cable Tie Width Max. (Imperial)	0.2"
	Cable Tie Width Max. (Metric)	5.2mm
	Height H (Imperial)	0.125"
	Height H (Metric)	3.2mm
	Mounting Hole Diameter D (Imperial)	0.14"
	Mounting Hole Diameter D (Metric)	3.7 mm
	Mounting Hole Centers (Imperial)	1.25"

151-24219



Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces
	Weight (Metric)	0.05kg