

151-24319

HellermannTyton

Article Number: 151-24319

Description: Cable Tie Mounting Plates, .50" x 4.25", T18-T50 Cable Ties, #6 (M3) Screw, PA66, Natural, 100/pk



Base Data		
	Local Order Number	MP3M3.NN3P
	Type	MP3M3
	Color	Natural (NA)
	Features and benefits	<ul style="list-style-type: none"> • Mounting plates allow multiple bundles to run parallel. • The mounts are secured using two screws, while the bundles are attached using cable ties in any of the available slots.
	Quantity Per	bag
	Product Description	Mounting Plates allow multiple cables to be run in parallel. Mounts are secured with two screws. Cables are attached to the plates by running a cable tie through any of the available slots.
	Short Description	Cable Tie Mounting Plates, .50" x 4.25", T18-T50 Cable Ties, #6 (M3) Screw, PA66, Natural, 100/pk
Product Dimensions		
	Length L (Imperial)	4.25"
	Length L (Metric)	108.0mm
	Fixation Method	Screw Mounting and Rivet
	Number of Bundles	3
	Width W (Imperial)	0.5"
	Width W (Metric)	12.7mm
	Cable Tie Width Max. (Imperial)	0.2"
	Cable Tie Width Max. (Metric)	5.2mm
	Height H (Imperial)	0.125"
	Height H (Metric)	3.2mm
	Mounting Hole Diameter D (Imperial)	0.15"
	Mounting Hole Diameter D (Metric)	3.7 mm
	Mounting Hole Centers (Imperial)	1.25"

151-24319



Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces