

151-27000

**HellermannTyton**



Article Number: 151-27000

Description: Low Profile Rivet Mount .938"X.47"-PA66, NA, Mnt Hole .25", Max Pan .134", T18-T50 Ties, 100/pk

Base Data		
	Local Order Number	LKCRF19C2
	Type	LKCRF1
	Color	Natural (NA)
	Features and benefits	<ul style="list-style-type: none"> <li>The low-profile rivet mount is designed to secure wiring bundles and fastens with the drive rivet through a predrilled hole.</li> <li>This mount is ideal for use in applications where space is limited.</li> </ul>
	Quantity Per	bag
	Product Description	HellermannTyton's Mounts with Rivets are ideal for use in applications where space is limited and is designed to secure wiring bundles. Fastens with the drive rivet through a predrilled hole.
	Short Description	Low Profile Rivet Mount .938"X.47"-PA66, NA, Mnt Hole .25", Max Pan .134", T18-T50 Ties, 100/pk
Product Dimensions		
	Length L (Imperial)	0.938"
	Length L (Metric)	24.0mm
	Fixation Method	with Rivet (Mounts)
	Width W (Imperial)	0.47"
	Width W (Metric)	12.0mm
	Height H (Imperial)	0.157"
	Height H (Metric)	3.99mm
	Panel Thickness Max. (Imperial)	0.134"
	Panel Thickness Max. (Metric)	3.40mm
	Mounting Hole Diameter D (Imperial)	0.25"
	Mounting Hole Diameter D (Metric)	6.4 mm
	Mounting Hole Diameter D Max. (Imperial)	0.255"

151-27000



Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100
	Customs Number(Schedule B)	3926909987