

151-29701

HellermannTyton



Article Number: 151-29701

Description: Axial Oval Mount, .31" Mounting Hole, PA66HIRHSUV, Black, 500/pkg

Base Data		
	Local Order Number	SAOM820HIRHSH1
	Type	SAOM82
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Positions bundles off cross members and frame rails to prevent abrasion and chafing. • Metal insert bushing accommodates high torque installation. • Made with high impact, heat stabilized, and UV material ideal for trucking and heavy equipment environments.
	Quantity Per	bag
	Product Description	HellermannTyton's axial oval mount stands off bundles from frame rails and cross members to prevent them from rubbing and chafing. The axial oval mount accommodates cable ties up to 0.5" wide. The hole on the mount was designed to fit a 5/16" bolt.
	Short Description	Axial Oval Mount, .31" Mounting Hole, PA66HIRHSUV, Black, 500/pkg
Product Dimensions		
	Length L (Imperial)	1.4"
	Length L (Metric)	34.3mm
	Fixation Method	Screw Mounting and Rivet
	Width W (Imperial)	1.0"
	Width W (Metric)	26.0mm
	Cable Tie Width Max. (Imperial)	0.5"
	Cable Tie Width Max. (Metric)	12.7mm
	Height H (Imperial)	1.40"
	Height H (Metric)	35.0mm
	Mounting Hole Diameter D (Metric)	8.0 mm
	Stud Diameter (Imperial)	0.3125"
	Stud Diameter (Metric)	8.0 mm

151-29701



Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat and UV-resistant (PA66HIRHSUV)
	Material Shortcut	PA66HIRHSW
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +230°F (-40°C to +110°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500
	Package Quantity (Metric)	500Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces
	Weight (Metric)	10.8kg